

Switch

Save twice:

Costs & CO₂ emissions

Ultra concentrate

Savings from lower use of cleaning agent and less storage space



Reduced resource consumption & performance assurance certified by EU Ecolabel

Integrated dosing cap

Efficient cleaning processes & savings on dosing equipment



Safe handling of ultra concentrates & overdose prevention

Refill pouch

Cost-effective refilling with the one-litre pouch



Outstanding: 100% recyclable & 85% less packaging volume



Switch

Easy application:

1. Turn bottle upside down with the lever in neutral position.
2. Turn the lever away from you to fill the cap with 5 ml of formulation. (4 SEC.)
3. Turn the lever towards you, to let the formulation flow into the 4-litre bucket or the 750 ml spray bottle.
4. Remove the dosing cap to refill the bottle with the pouch.

Scan this code for the Switch system video instructions.

Small lever, big leverage

When you change to the new Switch system, your use of 10,000 litres of cleaning agents has the potential to avoid significant amounts of CO₂ emissions and crude oil and plastic consumption.

ZERTIFIKAT
GREEN CARE PERFORMANCE CALCULATOR

RESSOURCENEINSPARUNGEN

CO₂ EMISSIONEN: -4.330 kg

CRUDE OIL: -1.379 kg

PLASTIC: -738 kg

100% RECYCLABLE

-4,330 kg CO₂ emissions

-1,379 kg Crude oil

-738 kg Plastic

*Basis of calculation: SANET inoSwitch one-litre bottle

Tana-Chemie GmbH
Rheinallee 96
D-55120 Mainz
info@tana.de
+49 (0) 6131 / 964-03

A circular future | green-care-professional.com/switch

Cradle to Cradle Certified® is a registered trademark of the Cradle to Cradle Products Innovation Institute.



It's time to Switch

Reduce + Reuse + Recycle




A circular future | green-care-professional.com/switch






Bottle with dosing cap & refill pouch

The dosing cap for 5 ml formulation guarantees exact dosing.



200 dosages for the 4 L bucket



200 dosages for the 750 ml spray bottle



The bottle and cap made from 100% recyclate can be recycled completely.



Ultra-concentrated formulation meets the highest sustainability requirements and reduces use of cleaning agents.



Simple instructions: QR code linked to usage video

No use of barrier materials and adhesives for complete recyclability.

Printed area is separate from the pouch itself and fused to it only at the edges.

“Very good recyclability, which cannot be optimized any further”
Interseroh

Compared to a bottle, the pouch saves up to 85% packaging volume.

Outstanding:

The pouch, spout and printed sleeve are made of a mono-material (polyethylene or PE). The pouch can be 100% recycled to a high quality.



Highest praise from independent institutions for the refill pouch:



Our Switch portfolio



TANET uniSwitch
Ultra-concentrated floor and surface cleaner

716155 – 1 l BOTTLE** | 716230 – 1 l POUCH*



TAWIP vioSwitch
Ultra-concentrated floor cleaner and care

716156 – 1 l BOTTLE** | 716232 – 1 l POUCH*



SANET inoSwitch
Ultra-concentrated sanitary cleaner

716163 – 1 l BOTTLE** | 716231 – 1 l POUCH*



GREASE topSwitch
Ultra-concentrated multi-purpose kitchen cleaner

716160 – 1 l BOTTLE** | 716233 – 1 l POUCH*

